

# INTERNATIONAL PRODUCTS CORPORATION

201 CONNECTICUT DRIVE, BURLINGTON, NJ 08016  
(609)386-8770 Fax: (609)386-8438 www.ipcol.com

## MICRO-90® FILTER MEMBRANE COMPATIBILITY

100% MICRO-90, Room Temperature, 24 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
100% Micro-90	Δ Mass	0.0%	0.0%	-0.1%	0.3%	0.1%	0.0%	0.0%
	Δ Surface Area	0.0%	0.2%	0.1%	0.6%	0.0%	0.0%	1.9%
Water (Control)	Δ Mass	0.7%	0.2%	0.1%	0.4%	0.3%	-0.1%	0.0%
	Δ Surface Area	0.0%	0.2%	0.2%	1.0%	0.0%	0.0%	2.3%

2% MICRO-90, Room Temperature, 24 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
2% Micro-90	Δ Mass	0.0%	0.1%	0.1%	0.4%	0.4%	0.1%	0.1%
	Δ Surface Area	0.0%	0.2%	0.1%	0.7%	0.0%	0.0%	0.5%
Water (Control)	Δ Mass	0.7%	0.2%	0.1%	0.4%	0.3%	-0.1%	0.0%
	Δ Surface Area	0.0%	0.2%	0.2%	1.0%	0.0%	0.0%	2.3%

100% MICRO-90, 40C, 24 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
100% Micro-90	Δ Mass	0.0%	0.1%	-0.1%	0.4%	-0.1%	0.1%	0.0%
	Δ Surface Area	0.0%	0.3%	0.2%	1.0%	0.1%	0.0%	-0.3%
Water (Control)	Δ Mass	0.7%	0.2%	0.1%	0.4%	0.3%	-0.1%	0.0%
	Δ Surface Area	0.0%	0.2%	0.2%	1.0%	0.0%	0.0%	2.3%

2% MICRO-90, 40C, 24 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
2% Micro-90	Δ Mass	-0.2%	0.2%	0.4%	1.0%	0.3%	0.6%	0.1%
	Δ Surface Area	0.0%	0.3%	0.2%	1.4%	0.0%	0.0%	0.5%
Water (Control)	Δ Mass	0.7%	0.2%	0.1%	0.4%	0.3%	-0.1%	0.0%
	Δ Surface Area	0.0%	0.2%	0.2%	1.0%	0.0%	0.0%	2.3%

100% MICRO-90, Room Temperature, 288 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
100% Micro-90	Δ Mass	-0.2%	0.1%	-0.2%	1.0%	0.0%	0.1%	-6.9%
	Δ Surface Area	0.0%	0.6%	0.2%	1.7%	0.0%	0.0%	-0.4%
Water (Control)	Δ Mass	0.9%	0.2%	0.1%	1.5%	0.3%	0.0%	0.0%
	Δ Surface Area	0.0%	0.6%	0.4%	2.7%	0.0%	0.1%	-0.5%

2% MICRO-90, Room Temperature, 288 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
2% Micro-90	Δ Mass	-0.1%	0.2%	0.2%	1.4%	0.2%	0.3%	0.0%
	Δ Surface Area	0.0%	0.6%	0.3%	2.5%	0.0%	0.0%	-0.8%
Water (Control)	Δ Mass	0.9%	0.2%	0.1%	1.5%	0.3%	0.0%	0.0%
	Δ Surface Area	0.0%	0.6%	0.4%	2.7%	0.0%	0.1%	-0.5%

100% MICRO-90, 40C, 288 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
100% Micro-90	Δ Mass	-0.4%	0.5%	0.0%	1.2%	0.1%	0.1%	-3.8%
	Δ Surface Area	0.0%	1.1%	0.3%	3.1%	0.1%	0.0%	-1.7%
Water (Control)	Δ Mass	0.7%	0.5%	0.1%	2.7%	0.4%	0.3%	0.0%
	Δ Surface Area	0.0%	0.8%	0.4%	4.5%	0.0%	0.0%	-3.6%

2% MICRO-90, 40C, 288 Hours

		Polypropylene	Polyamide imide	Polysulfone	Polyaramide	Zirconia	Alumina	Cellulose Acetate
2% Micro-90	Δ Mass	-0.5%	0.5%	0.5%	2.2%	0.3%	0.3%	-3.7%
	Δ Surface Area	0.0%	0.8%	0.4%	4.3%	0.0%	0.0%	-4.6%
Water (Control)	Δ Mass	0.7%	0.5%	0.1%	2.7%	0.4%	0.3%	0.0%
	Δ Surface Area	0.0%	0.8%	0.4%	4.5%	0.0%	0.0%	-3.6%

**For Sales in Europe:**

020-8857-5678 Fax: 020-8857-1313

Unit 5, Green Lane Business Park, 238 Green Lane, London SE9 3TL, UK